

Unruly particulate challenges? We've got you covered.



A. KLEENGUARD* A40 Liquid & Particle Protection Apparel

Provides better liquid and particulate barriers—excellent replacement for Tyvek®. Passes NFPA 99 Criteria for antistatic materials. Meets ANSI/ISEA 101-1996 sizing standard. White.

| No. | Size | Case Qty. | Case |
|---------------------|----------|-----------|------|
| Zipper Front | | | |
| KCC 44303 | Large | 25 | |
| KCC 44304 | X-Large | 25 | |
| KCC 44305 | 2X-Large | 25 | |

Zipper Front; Elastic Wrists & Ankles

| | | | |
|-----------|----------|----|--|
| KCC 44313 | Large | 25 | |
| KCC 44314 | X-Large | 25 | |
| KCC 44315 | 2X-Large | 25 | |

Zipper Front; Elastic Wrists & Ankles; Hood

| | | | |
|-----------|----------|----|--|
| KCC 44323 | Large | 25 | |
| KCC 44324 | X-Large | 25 | |
| KCC 44325 | 2X-Large | 25 | |

Zipper Front; Elastic Back, Wrists & Ankles; Hood & Boots

| | | | |
|-----------|----------|----|--|
| KCC 44334 | X-Large | 25 | |
| KCC 44335 | 2X-Large | 25 | |

B. KLEENGUARD* A30 Breathable Splash & Particle Protection Apparel

Patented Microforce™ barrier fabric with superior particulate holdout and excellent breathability. Made of heavier fabric for more durability. Ideal for automotive and assembly operation. White.

| No. | Size | Case Qty. | Case |
|---|----------|-----------|------|
| Zipper Front w/1" Flap; Elastic Back | | | |
| KCC 46004 | X-Large | 25 | |
| KCC 46005 | 2X-Large | 25 | |

Zipper Front w/1" Flap; Elastic Back, Wrists & Ankles

| | | | |
|-----------|----------|----|--|
| KCC 46103 | Large | 25 | |
| KCC 46104 | X-Large | 25 | |
| KCC 46105 | 2X-Large | 25 | |

Zipper Front w/1" Flap; Elastic Back, Wrists & Ankles; Hood

| | | | |
|-----------|----------|----|--|
| KCC 46114 | X-Large | 25 | |
| KCC 46115 | 2X-Large | 25 | |
| KCC 46117 | 4X-Large | 21 | |

C. KLEENGUARD* A60 Bloodborne Pathogen & Chemical Splash Protection Apparel

Three-layer fabric construction features a middle layer of microporus film that allows heat and sweat vapor to escape while protecting against dry particulates and liquid. Passes ASTM F1670/1671± testing for penetration of blood, body fluids and blood-borne pathogens. Denim Blue.

| No. | Size | Case Qty. | Case |
|--|----------|-----------|------|
| Zipper Front; Storm Flap; Elastic Back, Wrists & Ankles | | | |
| KCC 45003 | Large | 24 | |
| KCC 45004 | X-Large | 24 | |
| KCC 45005 | 2X-Large | 24 | |

Zipper Front; Storm Flap; Elastic Back, Wrists & Ankles; Hood

| | | | |
|-----------|----------|----|--|
| KCC 45023 | Large | 24 | |
| KCC 45024 | X-Large | 24 | |
| KCC 45025 | 2X-Large | 24 | |

Zipper Front; Storm Flap; Elastic Back, Wrists & Ankles; Hood & Boots

| | | | |
|-----------|----------|----|--|
| KCC 45094 | X-Large | 24 | |
| KCC 45095 | 2X-Large | 24 | |



A



B



C



How to choose coveralls

1. When should I use KLEENGUARD* A40 Liquid & Particle Protection Apparel?

For general protection from nonhazardous liquids.

2. When should I use KLEENGUARD* A30 Breathable Splash & Particle Protection Apparel?

For protection when working in or with pharmaceutical research, laboratories, fine particle contamination, fiberglass/heavy dust environments, pesticides and aerospace.

3. When should I use KLEENGUARD* A60 Bloodborne Pathogen & Chemical Splash Protection Apparel?

For wet jobs in crime scene cleanup, emergency medical response, embalming/forensics, nuclear facilities, tank cleaning, fiberglass handling, utilities, manufacturing plants, rubber manufacturing and farm and agricultural settings.